



How to Select your Glock Front Sight Height

NOTE: NONE OF THE BELOW TO BE USED WITH MODULAR OPTIC SYSTEM (MOS)

.215 TALL FRONT SIGHTS FOR USE WITH BELOW GEN 1, 2 & 3 MODELS:

GLOCK MODEL IMPRINTED ON YOUR SLIDE

- | | | |
|-------------------------------|----------------|-----------------------|
| G17 Standard | G23 Compact | G42 Subcompact |
| G19 Compact | G26 Subcompact | G43 Subcompact |
| G20 SF (Short Frame) Standard | G32 Compact | G43X Gen 5 Subcompact |
| G21 SF Standard | G37 Standard | G45 Compact |
| G22 Standard | G38 Compact | G48 Gen 5 Compact |

.245 TALL FRONT SIGHTS FOR USE WITH GEN 4 & GEN 5 MODELS:

GLOCK MODEL & GEN NUMBERS ARE IMPRINTED ON YOUR SLIDE

- | | | | |
|--------------------|---------------------|---------------------|----------------------|
| G17 Gen4 Standard | G20 Gen4 Standard | G26 Gen5 Subcompact | G32 Gen4 Compact |
| G17 Gen5 Standard | G21 Gen4 Standard | G27 Gen4 Subcompact | G33 Gen4 Subcompact |
| G17C Gen4 Standard | G22 Gen4 Standard | G29 Gen4 Subcompact | G34 Gen4 Competition |
| G19 Gen4 Compact | G23 Gen4 Compact | G30 Gen4 Subcompact | G35 Gen4 Competition |
| G19 Gen5 Compact | G26 Gen4 Subcompact | G31 Gen4 Standard | G41 Gen4 Competition |
| | | | G44 Compact |

.245 TALL FRONT SIGHTS FOR USE WITH FOLLOWING GEN 1, 2 & 3 MODELS:

- | | | |
|-----------------|-------------------|-----------------|
| G17L Long Slide | G29 SF Subcompact | G33 Subcompact |
| G19X Compact | G30S Subcompact | G34 Competition |
| G24 Long Slide | G30 SF Subcompact | G35 Competition |
| G27 Subcompact | G31 Standard | G36 Subcompact |
| | | G39 Subcompact |